



# NANOFLOW MAX

## Fiber blowing machine for FTTH fibers (EPFU) and micro cables up to 4.5 mm

#### Adjustable clamping force

Secures grip around cable/fiber during installation.

#### **Tool free installation**

Easy to open and close by hand with quick load of fiber and duct. Adjustable speed and torque. Battery-powered (independent of 100V/240V).

#### **LED display**

Showing speed, distance, fiber protection and battery information.

#### Unique fiber protection technology

If the maximum recommended load on the fiber exceeds the preset torque, the machine stops the blowing process immediately without damaging the fiber.

#### Tested in accordance to IEC standards

#### **INCLUDED**

- 2 x 24V 2.0 Ah Lithium-ion battery with quick charger
- Filter and water separator
- 1 adaptor plate set.
- MAX steel drive wheel for fibers +3 mm
- Drive wheel for fibers 0.8-3 mm
- Duct adaptors for 3, 5, 7, 8, 8.5, 10, 12, 12.7 mm
- Quality transport box

#### POSSIBLE ADD-ONS

Service Agreement with Extended Warranty

Tripod with quick adaptor

Item No.: 103-161127005

Shoulder strap

Item No.: 103-160601074

Reel holder arm for pre-connected fiber

Item No.: 103-171020001

A wide selection of adaptor plates for any fiber/duct sizes on request


#### **SPECIFICATIONS**

Item No.: Cable diameter: Duct diameter: Blowing distance <sup>1</sup> : Blowing speed <sup>2</sup> : Pushing force: Max. Pressure: Recommended airflow <sup>3</sup> : Weight: Length:	
	104 mm

- <sup>1)</sup>Depending on type of microduct and cable size. Blowing distance is reduced when blowing fibers above 3 mm.
- <sup>2)</sup> Depending on type of microduct and cable.
- 2) Cooled and dried air.



# **NANOFLOW MAX**



### Adaptor plates and wheel guide

For fiber size 0.8 - 3.0 mm NanoFlow adaptor plates and drive wheel applies



For micro cable size 3.0 - 4.5 mm NanoFlow MAX adaptor plates and MAX steel wheel applies.



#### **WARNING:**

Do <u>not</u> combine NanoFlow MAX adaptor plates/MAX steel drive wheel with NanoFlow adaptor plates/drive wheel. Only use MAX adaptor plates with MAX steel drive wheel. Look for the written text 'MAX' if in doubt. If you mix the adaptor plates, it can make the machine malfunction.

